



Representative Image

**Alternate Catalog No. SU203MR-K1.6**  
**Catalog No. 2CDS273347R0257**

**Description:** MCB SU200MR RTT 3P K 1.6A BCP

**UPC No 4016779958271**

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU203MR-K1,6 MCB K-Char., 10kA, 1,6A, 3P, RTT UL 489, Ring Cable Lug

## Descriptors

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

## Specifications

|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA   |
| Number of Poles                   | 3                                            |
| Power Loss                        | at Rated Operating Conditions per Pole 1.8 W |
| Product Main Type                 | SU200MR                                      |
| Rated Current                     | 1.6 A                                        |
| Rated Voltage (V)                 | (480Y / 277 V AC)<br>(96 V DC)               |
| Tripping Characteristic           | K                                            |