



Representative Image

Catalog No. 9T51B0090

Description: "1C,1kVA,600-120/240,100C,3R,60Hz,QB"

UPC No 783173008485

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	600
SecVoltage	120/240
KVA	1 KVA
Coil Material	CU
TempRise	100.0 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	12225
Net Weight	25
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	25
Sound	Std
GSA Compliance	Yes

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	7.9 in
Depth	5.5 in
Height	9.6 in