



Representative Image

### Catalog No. 9T21B9120

Description: "1A,25kVA,208-120/240,115C,N3R,QMS"

UPC No 783173803400

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

#### Descriptors

|             |                                           |
|-------------|-------------------------------------------|
| Category    | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T7                                        |

#### Specifications

|                |          |
|----------------|----------|
| Phase          | 1        |
| PriVoltage     | 208      |
| SecVoltage     | 120/240  |
| KVA            | 25.0 KVA |
| Coil Material  | AL       |
| TempRise       | 115.0 °C |
| ElecShield     | N        |
| Sub Type       | Standard |
| Frequency      | 60 Hz    |
| Impedance      | 2.4 %    |
| FrameSize      | 50500    |
| Net Weight     | 388 lb   |
| TempClass      | 180.0 °C |
| AmbTemp        | 40.0 °C  |
| InsulSys       | IS-12    |
| KFactor        | K1       |
| Enclosure Type | NEMA 3R  |
| Net Weight     | 388 lb   |
| GSA Compliance | No       |

#### Classifications

|     |     |
|-----|-----|
| UL  | Yes |
| cUL | Yes |
| CE  | No  |

**Dimensions**

|        |         |
|--------|---------|
| Width  | 16.8 in |
| Depth  | 16.0 in |
| Height | 20.9 in |