

**Alternate Catalog No. SU203MR-K0.2**  
**Catalog No. 2CDS273347R0087**

**Description:** MCB SU200MR RTT 3P K 0.2A BCP

**UPC No** 4016779958172

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU203MR-K0.2 MCB K-Char., 10kA, 0.2A, 3P, RTT UL 489, Ring Cable Lug

Representative Image

**Descriptors**

|          |                            |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

**Specifications**

|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| Number of Poles                   | 3                                            |
| Tripping Characteristic           | K                                            |
| Rated Current                     | 0.20 A                                       |
| Product Main Type                 | SU200MR                                      |
| Rated Voltage (V)                 | (480Y / 277 V AC)<br>(96 V DC)               |
| Interrupting Rating acc. to UL489 | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA   |
| Power Loss                        | at Rated Operating Conditions per Pole 1.7 W |