

Alternate Catalog No. SU201MR-K63
Catalog No. 2CDS271347R0607

Description: MCB SU200MR RTT 1P K 63A BCP

UPC No 4016779956673

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU201MR-K63 MCB K-Char., 10kA, 63A, 1P, RTT UL 489, Ring Cable Lug



Representative Image

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	1
Tripping Characteristic	K
Rated Current	63 A
Product Main Type	SU200MR
Rated Voltage (V)	(240 V AC) (48 V DC)
Interrupting Rating acc. to UL489	(240 V AC) 10 kA (48 V DC) 10 kA
Power Loss	at Rated Operating Conditions per Pole 5.4 W