



Representative Image

## Catalog No. 9T51B0085

**Description:** "1C,0.15kVA,600-120/240,55C,3R,60Hz,QB"

**UPC No** 783173008461

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

### Descriptors

|             |                                           |
|-------------|-------------------------------------------|
| Category    | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T5                                        |

### Specifications

|                  |          |
|------------------|----------|
| Phase            | 1        |
| PriVoltage       | 600      |
| SecVoltage       | 120/240  |
| KVA              | 0.15 KVA |
| Coil Material    | CU       |
| TempRise         | 55.0 °C  |
| ElecShield       | N        |
| Sub Type         | Standard |
| Frequency        | 60 Hz    |
| FrameSize        | 8175     |
| Net Weight       | 10       |
| TempClass        | 105.0 °C |
| AmbTemp          | 40.0 °C  |
| InsulSys         | CLASSA   |
| EnergyEfficiency | None     |
| KFactor          | K1       |
| Enclosure Type   | NEMA 3R  |
| Net Weight       | 10       |
| Sound            | Std      |
| GSA Compliance   | Yes      |

### Classifications

|     |     |
|-----|-----|
| UL  | Yes |
| cUL | Yes |
| CE  | No  |

| Dimensions |        |
|------------|--------|
| Width      | 6.1 in |
| Depth      | 4.2 in |
| Height     | 7.4 in |