



Representative Image

Catalog No. A1A22080RM

Description: A1A 80A 2P 10KAIC RELIAMOD BREAKER UL

UPC No 783164673234

Home > Modular Metering > ReliaMod > ReliaMod Tenant Breaker

Descriptors

Category	ReliaMod Tenant Breaker
----------	-------------------------

Specifications

Tenant Breaker Amperage	80 A
Tenant Breaker Poles	2P
Tenant Breaker Phase	1-Phase
Tenant Breaker Voltage	240V Max
Tenant Breaker kAIC (@240V)	10
Tenant Breaker Load Lugs Cu/Al (Factory Installed)	(1) #14-#2
Additional Notes	ReliaMod Formula A1/A2 tenant breakers can only be used in 225A socket meter stacks that accept 10-22KAIC tenant breakers only