

Catalog No. 9T58K1835

Description: "1C,3kVA,600-120/240,115C,C&C,CLO,IP"

UPC No 783173155714

Home > Transformers > Dry Type, Encapsulated Core & Coil > Control Power

ABB's General purpose encapsulated open core, and coil transformer (also known as Type IP Control Power transformers) are ideally suited for industrial and light-duty loads, HVAC applications, signal and alarm systems, industrial control panels, lighting, and circuit isolation. The optional fuse block adapter kits enable input and output flexibility. Type IP Control Power transformers are an economical alternative to high in-rush/machine tool transformers.

Representative Image

Descriptors

Category	Control Power
GO Schedule	TQ

Specifications

Phase	1
PriVoltage	600
SecVoltage	120/240
KVA	3.0 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
Sub Type	CONTROL LEADS OUT
Frequency	60 Hz
FrameSize	14475
Net Weight	45
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
EnergyEfficiency	None
KFactor	K1
Enclosure Type	None
Net Weight	45
Sound	Std
GSA Compliance	No
PriRatingType	8
SecRatingType	8
Outline	303B947ABP14475
TransType	IP

Classifications

UL	Yes
----	-----

Classifications

cUL	Yes
CE	No

Dimensions

Width	6.8 in
Depth	8.8 in
Height	5.8 in