

**Alternate Catalog No. SU204M-C32**  
**Catalog No. 2CDS274337R0324**

**Description:** UL489 MCB 4P C 32A 480/277

**UPC No 4016779931601**

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU204M-C32 Miniature Circuit Breaker C-Char., 10kA, 32A, 4P UL489



Representative Image

**Descriptors**

|          |                            |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

**Specifications**

|                                                |                                                        |
|------------------------------------------------|--------------------------------------------------------|
| Number of Poles                                | 4                                                      |
| Tripping Characteristic                        | C                                                      |
| Rated Current                                  | 32 A                                                   |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489             |
| Product Main Type                              | SU200M                                                 |
| Rated Voltage (V)                              | (480Y / 277 V AC)<br>(96 V DC)                         |
| Interrupting Rating acc. to UL489              | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA             |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                       |
| Power Loss                                     | 14,8 W<br>at Rated Operating Conditions per Pole 3,7 W |