



Representative Image

## Catalog No. 9T21B1004G24

**Description:** "1A,5kVA,240x480-120/240,115C,3R,Carrier"

**UPC No** 783173107096

**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

### Descriptors

|             |                                           |
|-------------|-------------------------------------------|
| Category    | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T7                                        |

### Specifications

|                |          |
|----------------|----------|
| Phase          | 1        |
| PriVoltage     | 240x480  |
| SecVoltage     | 120/240  |
| KVA            | 5.0 KVA  |
| Coil Material  | AL       |
| TempRise       | 115.0 °C |
| ElecShield     | N        |
| Sub Type       | Standard |
| Frequency      | 60 Hz    |
| FrameSize      | 16350    |
| Net Weight     | 103      |
| TempClass      | 180.0 °C |
| AmbTemp        | 40.0 °C  |
| InsulSys       | IS-12    |
| KFactor        | K1       |
| Enclosure Type | NEMA 3R  |
| Net Weight     | 103      |
| GSA Compliance | No       |

### Classifications

|     |     |
|-----|-----|
| UL  | Yes |
| cUL | Yes |
| CE  | No  |

### Dimensions

|       |         |
|-------|---------|
| Width | 10.6 in |
|-------|---------|

**Dimensions**

|        |         |
|--------|---------|
| Depth  | 11.0 in |
| Height | 14.5 in |