



### Main

|                             |                                                             |
|-----------------------------|-------------------------------------------------------------|
| Range of Product            | 9007                                                        |
| Series name                 | Miniature potted                                            |
| Product or Component Type   | Limit switch lever                                          |
| Device short name           | 9007MS/ML                                                   |
| Associated complete product | 9007ML04..<br>9007MS04..                                    |
| Movement of operating head  | Rotary                                                      |
| Type of operator            | Cast zinc spring return roller lever 0.88 in (22.35 mm) -   |
| Type of roller              | 1 nylon outside roller 0.75 in (19.05 mm) 0.25 in (6.35 mm) |
| Type of approach            | Lateral approach                                            |
| Positive opening            | Without                                                     |

### Complementary

|                  |                      |
|------------------|----------------------|
| Tracks           | 1.375 in             |
| Switch actuation | By 30° cam           |
| Net Weight       | 0.1 lb(US) (0.05 kg) |

### Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient Air Temperature for Operation | -40...221 °F (-40...105 °C) |
| Ambient Air Temperature for Storage   | -40...221 °F (-40...105 °C) |
| Environmental characteristic          | Standard environment        |

### Ordering and shipping details

|                   |                                      |
|-------------------|--------------------------------------|
| Category          | 22421-LIMIT SWITCHES,ARMS FOR 9007MS |
| Discount Schedule | DS1                                  |
| GTIN              | 785901215974                         |
| Returnability     | No                                   |
| Country of origin | MX                                   |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type of Package 1       | PCE                 |
| Number of Units in Package 1 | 1                   |
| Package 1 Height             | 2.54 in (6.452 cm)  |
| Package 1 Width              | 1.00 in (2.54 cm)   |
| Package 1 Length             | 6.45 in (16.387 cm) |
| Package 1 Weight             | 1.60 oz (45.359 g)  |

### Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| RECh Regulation           |  RECh Declaration                                                                                                                                                                                                                                                                              |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope                                                                                                                                                                                                                                                                                                                                        |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|