



Main

Range of Product	9007
Series name	Miniature potted
Product or Component Type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007MS04.. 9007ML04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 1.38 in (35.05 mm) -
Type of roller	1 nylon outside roller 0.75 in (19.05 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22421-LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	785901215998
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	6.50 in (16.5 cm)
Package 1 Weight	0.80 oz (22.7 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh Regulation	RECh Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty	18 months
----------	-----------