

Product data sheet

Characteristics

7F1N

Limit switch lever, 9007, 9007MS/ML zinc, fixed length, outside nylon roller



Main

Range of Product	9007
Series name	Miniature potted
Product or Component	Limit switch lever
Type	
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 1.5 in (38.10 mm) -
Type of roller	1 nylon outside roller 0.75 in (19.05 mm) 0.75 in (19.05 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22421-LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	785901216247
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	1.60 oz (45.359 g)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

REACH Regulation

 [REACH Declaration](#)

EU RoHS Directive

Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty

18 months