



**Main**

Range of Product	9007
Series name	Miniature potted
Product or Component Type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 1.5 in (38.10 mm) -
Type of roller	1 nylon inside roller 0.75 in (19.05 mm) 1 in (25.40 mm)
Type of approach	Lateral approach
Positive opening	Without

**Complementary**

Tracks	0.875 in
Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

**Environment**

Ambient Air Temperature for Operation	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Environmental characteristic	Standard environment

**Ordering and shipping details**

Category	22421-LIMIT SWITCHES,ARMS FOR 9007MS
Discount Schedule	DS1
GTIN	785901280392
Returnability	Yes
Country of origin	MX

**Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.30 in (3.3 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	7.01 in (17.8 cm)
Package 1 Weight	1.28 oz (36.3 g)

## Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

REACH Regulation

 [REACH Declaration](#)

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)

Mercury free

Yes

RoHS exemption information

 Yes

## Contractual warranty

Warranty

18 months