

Product data sheet

Characteristics

9007A

NEMA limit switch, 9007C, low differential spring return rotary lever arm head



Main

Range of Product	9007
Series name	Heavy duty
Product or Component	Limit switch head
Type	
Device short name	9007C
Head type	Rotary head
Product Compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Rotary
Type of operator	Spring return without operating lever zinc low differential
Type of approach	Lateral approach, 1 or 2 programmable direction
Positive opening	Without

Complementary

Switch actuation	CW and CCW From left and right
Net Weight	0.41 lb(US) (0.19 kg)

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901500889
Nbr. of units in pkg.	1
Package weight(Lbs)	6.72 oz (190.5 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.81 in (4.6 cm)
Package 1 width	1.89 in (4.8 cm)
Package 1 Length	2.99 in (7.6 cm)

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

REACH Regulation

 [REACH Declaration](#)

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)

Mercury free

Yes

RoHS exemption information

 Yes

Contractual warranty

Warranty

18 months