



Main

Range of Product	9007
Series name	Heavy duty
Device short name	C
Head type	Turret head rotary lever
Type of operator	Spring return lever arm standard pre-travel) to be ordered separately Drive shaft reduced diameter to 0.306 in)lever arm
Switch actuation	CW
Cable entry	NPT conduit entry 0.5 in (12.70 mm)
Contacts type and composition	1 NO/1 NC
Contact operation	Snap action

Complementary

Body Material	Zinc alloy
Switch Function	SPDT-DB
Contact form	Form Z
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	4 lbf.in (0.45 N.m)
Tripping angle	4 °
Maximum displacement angle	90 °
[Ie] rated operational current	10 A, A600 10 A, Q600
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V
Local signalling	Without pilot light
Product Certifications	UL Listed CSA CE
Provided equipment	Receptacle

Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901046035
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.60 in (4.064 cm)
Package 1 Width	2.70 in (6.858 cm)
Package 1 Length	4.20 in (10.668 cm)
Package 1 Weight	20.00 oz (566.991 g)

Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

REACH Regulation

 [REACH Declaration](#)

EU RoHS Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

 [Product Environmental Profile](#)

Contractual warranty

Warranty

18 months