

# Product data sheet

## Characteristics

# 9007C54B

NEMA limit switch, 9007C, heavy duty, standard, spring return lever, standard pretravel, 10A, 600V, 1NO/1NC, NEMA 4, 13



### Main

Range of Product	9007
Series name	Heavy duty
Head type	Rotary head
Type of operator	Spring return lever arm standard pre-travel) to be ordered separately
Switch actuation	CW
Cable entry	NPT conduit entry 0.5 in (12.70 mm)
Contacts type and composition	1 NO/1 NC
Contact operation	Snap action

### Complementary

Body Material	Zinc alloy
Switch Function	SPDT-DB
Contact form	Form Z
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	4 lbf.in (0.45 N.m)
[Ie] rated operational current	10 A, A600 10 A, Q600
[Ui] rated insulation voltage	600 V
Local signalling	without
Product Certifications	CE UL Listed CSA
Provided equipment	Receptacle

### Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901500735
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	21.16 oz (600.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	4.90 in (12.446 cm)
Package 2 Width	5.80 in (14.732 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Package 2 Length	9.00 in (22.86 cm)
Package 2 Weight	12.63 lb(US) (5.729 kg)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------