

Product data sheet

Characteristics

9007C54CS17L3

NEMA limit switch, 9007C, heavy duty, standard, spring return lever, special



Main

Range of Product	9007
Series name	Heavy duty
Device short name	C
Head type	Turret head rotary lever
Material	Stainless steel
Type of operator	Spring return lever arm to be ordered separately maintained
Switch actuation	CW and CCW
Cable entry	NPT conduit entry 0.5 in (12.70 mm)
Contacts type and composition	1 NO/1 NC
Contact operation	Snap action

Complementary

Body Material	Zinc alloy
Switch Function	SPDT-DB
Contact form	Form Z
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	3 lbf.in (0.34 N.m)
Tripping angle	45 °
Maximum displacement angle	90 °
[Ie] rated operational current	10 A, A600 10 A, Q600
[Ui] rated insulation voltage	600 V
Product Certifications	UL Listed CSA CE
Provided equipment	Receptacle

Environment

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
Environmental characteristic	Chemical pollution resistance

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901046059
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	20.00 oz (566.991 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------