



**Main**

Range of Product	9007
Series name	Heavy duty
Device short name	C
Head type	Turret head rotary lever
Type of operator	Spring return lever arm to be ordered separately maintained
Switch actuation	CW and CCW
Cable entry	NPT conduit entry 0.5 in (12.70 mm)
Contacts type and composition	1 NO/1 NC
Contact operation	Snap action

**Complementary**

Body Material	Zinc alloy
Switch Function	SPDT-DB
Contact form	Form Z
Contacts material	Silver alloy (Ag/Ni)
Minimum torque for tripping	3 lbf.in (0.34 N.m)
Tripping angle	45 °
Maximum displacement angle	90 °
[Ie] rated operational current	10 A, A600 10 A, Q600
[Ui] rated insulation voltage	600 V
Product Certifications	CE CSA UL Listed
Provided equipment	Receptacle

**Environment**

Ambient air temperature for operation	-20...185 °F (-29...85 °C)
---------------------------------------	----------------------------

**Ordering and shipping details**

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901046042
Returnability	No
Country of origin	MX

**Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	20.00 oz (566.991 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------