



Main

Device short name	C
Head type	Type C turret head rotary lever
Provided equipment	Receptacle
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body Material	Zinc alloy
Cable entry	0.5 in (12.70 mm) NPT conduit entry
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Contacts type and composition	2 NO/2 NC two stage
Maximum displacement angle	90 °
Pilot light	Without pilot lamp
Specificity of operator	First stage : 10° - second stage : 2.5° Standard pre-travel
Switch actuation	CCW
Torque Value	4 lbf.in (0.45 N.m)
Tripping angle	4 °

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Environmental characteristic	Hazardous location
Product Certifications	UL Listed CE CSA

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901319337
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.99 in (17.742 cm)
Package 1 Width	2.75 in (6.985 cm)
Package 1 Length	17.74 in (45.064 cm)
Package 1 Weight	2.50 lb(US) (1.134 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------