



### Main

|                             |                                                                   |
|-----------------------------|-------------------------------------------------------------------|
| Range of Product            | 9007                                                              |
| Series name                 | Severe duty                                                       |
| Product or Component Type   | Limit switch lever                                                |
| Device short name           | 9007T/FT                                                          |
| Associated head             | 9007BS9<br>9007T5S9<br>9007NS9<br>9007AS9<br>9007T10S9<br>9007CS9 |
| Associated complete product | 9007T<br>9007C..S9<br>9007FT                                      |
| Movement of operating head  | Rotary                                                            |
| Type of operator            | Cast zinc spring return roller lever 1.5 in (38.10 mm) 0.75 in -  |
| Type of roller              | 1 steel outside offset roller 1 in (25.40 mm) 0.25 in (6.35 mm)   |
| Type of approach            | Lateral approach                                                  |
| Positive opening            | Without                                                           |

### Complementary

|                  |                      |
|------------------|----------------------|
| Switch actuation | By 30° cam           |
| Net Weight       | 0.1 lb(US) (0.05 kg) |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -10...185 °F (-23...85 °C) |
| Ambient Air Temperature for Storage   | -10...185 °F (-23...85 °C) |
| Environmental characteristic          | Standard environment       |

### Ordering and shipping details

|                   |                          |
|-------------------|--------------------------|
| Category          | 21494-9007 ARMS FOR FT,T |
| Discount Schedule | DS1                      |
| GTIN              | 785901760009             |
| Returnability     | No                       |
| Country of origin | MX                       |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type of Package 1       | PCE                 |
| Number of Units in Package 1 | 1                   |
| Package 1 Height             | 2.54 in (6.452 cm)  |
| Package 1 Width              | 1.00 in (2.54 cm)   |
| Package 1 Length             | 6.45 in (16.387 cm) |
| Package 1 Weight             | 1.60 oz (45.359 g)  |

Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          | <a href="#"> REACH Declaration</a>                                                                                                                                                                                                                                                               |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope                                                                                                                                                                                                                                                                                                                                        |
| Environmental Disclosure  | <a href="#"> Product Environmental Profile</a>                                                                                                                                                                                                                                                   |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|