



### Main

|                             |                                                               |
|-----------------------------|---------------------------------------------------------------|
| Range of Product            | 9007                                                          |
| Series name                 | Heavy duty                                                    |
| Product or Component Type   | Limit switch lever                                            |
| Device short name           | 9007C                                                         |
| Associated head             | 9007T10<br>9007C<br>9007T5<br>9007N<br>9007A<br>9007B         |
| Associated complete product | 9007AW<br>9007C                                               |
| Movement of operating head  | Rotary                                                        |
| Type of operator            | Flat steel spring return roller lever 2.5 in (63.50 mm)<br>-- |
| Type of roller              | 1 steel outside roller 0.63 in (16.00 mm) 0.63 in (16.00 mm)  |
| Type of approach            | Lateral approach                                              |
| Positive opening            | Without                                                       |

### Complementary

|                  |                      |
|------------------|----------------------|
| Switch actuation | By 30° cam           |
| Net Weight       | 0.1 lb(US) (0.05 kg) |

### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -20...185 °F (-29...85 °C) |
| Ambient Air Temperature for Storage   | -20...185 °F (-29...85 °C) |
| Environmental characteristic          | Standard environment       |

### Ordering and shipping details

|                   |                          |
|-------------------|--------------------------|
| Category          | 21493-9007 ARMS FOR AW,C |
| Discount Schedule | DS1                      |
| GTIN              | 785901781301             |
| Returnability     | No                       |
| Country of origin | MX                       |

### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type of Package 1       | PCE                 |
| Number of Units in Package 1 | 1                   |
| Package 1 Height             | 2.54 in (6.452 cm)  |
| Package 1 Width              | 1.00 in (2.54 cm)   |
| Package 1 Length             | 6.45 in (16.387 cm) |
| Package 1 Weight             | 1.60 oz (45.359 g)  |

Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          | <a href="#"> REACH Declaration</a>                                                                                                                                                                                                                                                               |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope                                                                                                                                                                                                                                                                                                                                        |
| Environmental Disclosure  | <a href="#"> Product Environmental Profile</a>                                                                                                                                                                                                                                                   |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|