



**Main**

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch lever
Device short name	9007C
Associated head	9007T5 9007N 9007B 9007A 9007C 9007T10
Associated complete product	9007C 9007AW
Movement of operating head	Rotary
Type of operator	Flat steel spring return roller lever without roller 3 in (76.20 mm) - -
Type of approach	Lateral approach
Positive opening	Without

**Complementary**

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

**Environment**

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

**Ordering and shipping details**

Category	21493-9007 ARMS FOR AW,C
Discount Schedule	DS1
GTIN	785901832102
Returnability	No
Country of origin	MX

**Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	1.60 oz (45.359 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------