



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch lever
Device short name	9007C
Associated head	9007T10 9007C 9007T5 9007A 9007B 9007N
Associated complete product	9007AW 9007C
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 3 in (76.20 mm) - -
Type of roller	1 steel inside roller 0.63 in (16.00 mm) 0.63 in (16.00 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21493-9007 ARMS FOR AW,C
Discount Schedule	DS1
GTIN	785901879206
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	1.60 oz (45.359 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------