

Product data sheet

Characteristics

9007E

NEMA limit switch, 9007C, top push rod plunger spring return head



Main

Range of Product	9007
Series name	Heavy duty
Product or Component	Limit switch head
Type	
Device short name	9007C
Head type	Plunger head
Product Compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Linear
Type of operator	Spring return plunger stainless steel -
Type of approach	Vertical approach, 1 direction
Positive opening	Without

Complementary

Switch actuation	On end
Net Weight	0.25 lb(US) (0.11 kg)

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Ambient Air Temperature for Storage	0...185 °F (-18...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901500827
Nbr. of units in pkg.	1
Package weight(Lbs)	4.16 oz (117.9 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.69 in (4.3 cm)
Package 1 width	1.89 in (4.8 cm)
Package 1 Length	2.99 in (7.6 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------