

Product data sheet

Characteristics

9007F

NEMA limit switch, 9007C, side roller plunger spring return head, vertical roller



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch head
Device short name	9007C
Head type	Plunger head
Product Compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Linear
Type of operator	Spring return side roller plunger with vertical roller steel vertical convertible to horizontal
Type of approach	Vertical approach, 2 directions
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net Weight	0.36 lb(US) (0.16 kg)

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Ambient Air Temperature for Storage	0...185 °F (-18...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901500780
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.69 in (4.3 cm)
Package 1 Width	1.89 in (4.8 cm)
Package 1 Length	2.99 in (7.6 cm)
Package 1 Weight	5.76 oz (163.3 g)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------