



### Main

|                            |                                                       |
|----------------------------|-------------------------------------------------------|
| Range of Product           | 9007                                                  |
| Series name                | Heavy duty                                            |
| Product or Component Type  | Limit switch head                                     |
| Device short name          | 9007C                                                 |
| Head type                  | Plunger head                                          |
| Product Compatibility      | 9007C                                                 |
| Associated lever           | 9007C                                                 |
| Associated body            | 9007C                                                 |
| Movement of operating head | Linear                                                |
| Type of operator           | Spring return side plunger stainless steel adjustable |
| Type of approach           | Lateral approach, 1 direction                         |
| Positive opening           | Without                                               |

### Complementary

|                  |                       |
|------------------|-----------------------|
| Switch actuation | On end                |
| Net Weight       | 0.36 lb(US) (0.16 kg) |

### Environment

|                                       |                          |
|---------------------------------------|--------------------------|
| Ambient Air Temperature for Operation | 0...185 °F (-18...85 °C) |
| Ambient Air Temperature for Storage   | 0...185 °F (-18...85 °C) |
| Environmental characteristic          | Standard environment     |

### Ordering and shipping details

|                   |                             |
|-------------------|-----------------------------|
| Category          | 21499-9007 C LIMIT SWITCHES |
| Discount Schedule | DS1                         |
| GTIN              | 785901500803                |
| Returnability     | No                          |
| Country of origin | MX                          |

### Packing Units

|                              |                      |
|------------------------------|----------------------|
| Unit Type of Package 1       | PCE                  |
| Number of Units in Package 1 | 1                    |
| Package 1 Height             | 7.62 in (19.355 cm)  |
| Package 1 Width              | 3.00 in (7.62 cm)    |
| Package 1 Length             | 19.35 in (49.161 cm) |
| Package 1 Weight             | 5.76 oz (163.293 g)  |

Offer Sustainability

|                           |                                                                                                                                                                                                                                                                                                                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          | <a href="#"> REACH Declaration</a>                                                                                                                                                                                                                                                               |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope                                                                                                                                                                                                                                                                                                                                        |
| Environmental Disclosure  | <a href="#"> Product Environmental Profile</a>                                                                                                                                                                                                                                                   |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|