



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch lever
Device short name	9007C
Associated head	9007T10 9007C 9007N 9007A 9007T5 9007B
Associated complete product	9007C 9007AW
Movement of operating head	Rotary
Type of operator	Cast zinc spring return adjustable bendable roller lever 0.88...4 in (22.35...101.60 mm) - -
Type of roller	1 nylon outside roller 2 in (50.80 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21493-9007 ARMS FOR AW,C
Discount Schedule	DS1
GTIN	785901818731
Nbr. of units in pkg.	1
Package weight(Lbs)	1.60 oz (45.359 g)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	7.40 in (18.796 cm)
Package 1 width	6.80 in (17.272 cm)
Package 1 Length	11.50 in (29.21 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------