

Product data sheet

Characteristics

9007KC

NEMA limit switch, 9007C, wobble stick head, coil spring extension



Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch head
Device short name	9007C
Head type	Multi-directional head
Product Compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Multi-directional
Type of operator	Spring return wobble stick steel coil spring extension
Type of approach	Multi-directional approach, multi-directional approach
Positive opening	Without

Complementary

Switch actuation	Any direction
Net Weight	0.48 lb(US) (0.22 kg)

Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Ambient Air Temperature for Storage	0...185 °F (-18...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21499-9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	785901543541
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.35 in (16.129 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	16.13 in (40.968 cm)
Package 1 Weight	7.68 oz (217.724 g)
Unit Type of Package 2	S03
Number of Units in Package 2	22
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.42 lb(US) (5.179 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------