



#### Main

Range of Product	9007
Series name	Heavy duty
Product or Component Type	Limit switch lever
Device short name	9007C
Associated head	9007C
Associated complete product	9007C
Movement of operating head	Rotary
Type of operator	Cast zinc stay put 90° forked arm with spring rods 2.5 in (63.50 mm) --
Type of approach	Lateral approach
Positive opening	Without

#### Complementary

Switch actuation	By any moving part
Net Weight	0.1 lb(US) (0.05 kg)

#### Environment

Ambient Air Temperature for Operation	-20...185 °F (-29...85 °C)
Ambient Air Temperature for Storage	-20...185 °F (-29...85 °C)
Environmental characteristic	Standard environment

#### Ordering and shipping details

Category	21493-9007 ARMS FOR AWC
Discount Schedule	DS1
GTIN	785901819639
Returnability	No
Country of origin	MX

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	7.60 in (19.304 cm)
Package 1 Weight	1.60 oz (45.359 g)

#### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

---

Warranty	18 months
----------	-----------

---