



Main

Range of Product	9012G
Pressure sensor type	Electromechanical pressure switch
Pressure sensor name	9012G
Pressure Rating	5600 psi (38610.64 kPa)
Maximum pressure	20000 psi
Contacts type and composition	2(NC-NO), DPDT-DB, Form ZZ, snap action, silver nickel contacts
Controlled fluid	Hydraulic oil -15...250 °F (-26...121 °C)) Non-corrosive liquids Air Non-corrosive gas
Fluid connection type	0.25 inch 18 NPTF UL 508
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Local display	Without

Complementary

Range on decreasing pressure	170...5600 psi (1172.11...38610.64 kPa)
Approx adjustable differential at mid range	289...1260 psi (1992.58...8687.39 kPa) +/- 2.5 % full scale
Cable entry	0.5 inch NPT conduit entrance
Terminal block type	8 screw terminals
Electrical connection	Screw-clamp terminals, AWG 22...AWG 12
Electrical circuit type	Control circuit
Local signalling	Without
Line Rated Current	3 A 240 V AC A600 NEMA rating designation 6 A 120 V AC A600 NEMA rating designation 0.22 A 125 V DC R300 NEMA rating designation 0.11 A 250 V DC R300 NEMA rating designation
Setting	Internal
Enclosure Material	Die cast aluminium alloy 380
Pressure actuator	Piston
Height	6.37 in (161.80 mm)
Depth	2.63 in (66.80 mm)
Width	3.5 in (88.90 mm)
Operating position	Any position
Materials in contact with fluid	303 stainless steel 440 stainless steel Viton fluorocarbon Teflon
Short-circuit protection	10 A cartridge overload and short-circuit protection gL
Maximum operating rate	120 cyc/mn
Mechanical durability	3000000 cycles
Repeat accuracy	4 %
Net Weight	3 lb(US) (1.36 kg)

Environment

Vibration resistance	2 gn 40...150 Hz)IEC 68-2-6
Shock resistance	50 gn IEC 58-2-27
Standards	CE UL 508 CSA C22.2 No 14
Product Certifications	UL listed file E12158 CCN NKPZ and CCN NTHT CE CSA LR25490 class 3211 03
NEMA degree of protection	NEMA 4/4X/13 UL 50
Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)

Ordering and shipping details

Category	21522-9012 G INDUSTRIAL PRESSURE SWITCHES
Discount Schedule	CP7G
GTIN	785901961345
Nbr. of units in pkg.	1
Package weight(Lbs)	3.00 lb(US) (1.361 kg)
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	9.50 in (24.13 cm)
Package 1 width	6.25 in (15.875 cm)
Package 1 Length	4.75 in (12.065 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------