

# Product data sheet

## Characteristics

### AP1

Limit switch lever, L100/300, aluminum, fixed length, center steel roller



#### Main

|                             |  |
|-----------------------------|--|
| Range of Product            | L100/300   |
| Series name                 | Severe duty  |
| Product or Component Type   | Limit switch lever   |
| Device short name           | L100/300   |
| Associated complete product | ML300<br>L100<br>L300<br>HML300<br>HL100<br>ML100<br>HL300<br>HML100 |
| Movement of operating head  | Rotary   |
| Type of operator            | Aluminium spring return roller lever 5 in (127.00 mm)<br>--          |
| Type of roller              | 1 steel center roller 1 in (25.40 mm) 0.25 in (6.35 mm)              |
| Type of approach            | Lateral approach   |
| Positive opening            | Without  |

#### Complementary

|                  |                      |
|------------------|----------------------|
| Switch actuation | By 30° cam           |
| Net Weight       | 0.1 lb(US) (0.05 kg) |

#### Environment

|                                       |                            |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -10...185 °F (-23...85 °C) |
| Ambient Air Temperature for Storage   | -10...185 °F (-23...85 °C) |
| Environmental characteristic          | Standard environment       |

#### Ordering and shipping details

|                   |                          |
|-------------------|--------------------------|
| Category          | 21519-9007 MISCELLANEOUS |
| Discount Schedule | DS1                      |
| GTIN              | 785901341963             |
| Returnability     | No                       |
| Country of origin | MX                       |

#### Packing Units

|                              |                     |
|------------------------------|---------------------|
| Unit Type of Package 1       | PCE                 |
| Number of Units in Package 1 | 1                   |
| Package 1 Height             | 5.30 in (13.462 cm) |
| Package 1 Width              | 7.00 in (17.78 cm)  |
| Package 1 Length             | 7.60 in (19.304 cm) |
| Package 1 Weight             | 1.60 oz (45.359 g)  |

## Offer Sustainability

|                           |   |
|---------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation          |  <a href="#">REACH Declaration</a>   |
| EU RoHS Directive         | Not applicable, out of EU RoHS legal scope  |
| Environmental Disclosure  |  <a href="#">Product Environmental Profile</a>   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|