

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	C
Enclosure type	Compact
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Specificity of operator	Low differential
Switch actuation	CW
Tilting angle	5 °
Torque value	4 lbf.in
Tripping angle	2 °

Environment

Ambient air temperature for operation	-20...185 °F
Product certifications	CE CSA UL listed

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901783336
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:

----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------