

Product data sheet

Characteristics

KA

Limit switch lever, L140, cable pull 1.5 emergency stop



Main

Range of Product	L140
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	L140
Associated complete product	L140
Movement of operating head	Rotary
Type of operator	Aluminium stay put lever for cable attachment 1.5 in (38.10 mm) for cable attachment, 1/4" pin, 3/4" inside diameter clearance
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By cable
Net Weight	0.1 lb(US) (0.05 kg)

Environment

Ambient Air Temperature for Operation	-10..185 °F (-23..85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	21519-9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	785901157809
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	7.99 in (20.3 cm)
Package 1 Weight	0.80 oz (22.7 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
