

Product data sheet

Characteristics

9007AW12M16

LIMIT SWITCH 600VAC 15AMP AW +OPTIONS

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Body type	Standard
Device short name	AW
Series name	Heavy duty

Complementary

Line Rated Current	15 A
Body material	Cast zinc
Contact operation	Snap action
Fluid connection type	0.5 inch BSP conduit entrance
Maximum displacement angle	30 °
Switch actuation	CCW
Tilting angle	5 °
Torque value	2.75 lbf.in
Tripping angle	2.5 °

Environment

Ambient air temperature for operation	-60...185 °F
NEMA degree of protection	NEMA 1/2/4/12/13
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21496 - 9007 AW PRECISION LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901607632
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and

----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------
