

Product data sheet

Characteristics

9007C54JS9

LIMIT SWITCH 600V 10AMP C SPECIAL +OPTI



Product availability: Stock - Normally stocked in distribution facility

Main

Body type	Standard plug-in
Device short name	C
Series name	Heavy duty

Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contact code designation	A600 Q600
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Snap action
Maximum displacement angle	90 °
Mounting location	Front Rear
Switch actuation	Any direction
Tilting angle	10 °
Torque value	3 lbf.in
Tripping angle	3 °
Type of operator	Delrin extension Spring return wobble stick

Environment

Ambient air temperature for operation	0...185 °F
NEMA degree of protection	NEMA 1/2/4/6/6P/12/13
Product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR

Ordering and shipping details

Category	21499 - 9007 C LIMIT SWITCHES
Discount Schedule	DS1
GTIN	00785901895688
Nbr. of units in pkg.	1
Package weight(Lbs)	1.25
Returnability	Y
Country of origin	MX

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------