




Main

Device short name	XCSTE
Enclosure type	Dust and damp proof enclosure indoor/outdoor Corrosion resistance enclosure indoor/outdoor

Complementary

Line Rated Current	6 A
[Us] rated supply voltage	24 V
Actuator	Key
Contact operation	Slow-break, break before make
Contacts type and composition	1 NO + 1 NC
Depth	1.3 in (33.02 mm)
Electromagnet interlocking	Locking on energisation and unlocking on de-energisation of solenoid
Enclosure material	Plastic
Height	3.67 in (93.22 mm)
Locking options description	With locking of actuator, unlocking by key operated lock With interlocking, locking by solenoid
Number of poles	2
Permissible voltage	300 V AC

Environment

Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
IP Degree of Protection	IP67
NEMA degree of protection	NEMA 4/4X/12

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110825435
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.33 in (11.0 cm)
Package 1 Width	1.38 in (3.5 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	17.64 oz (500.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------