




Main

Range of Product	Telemecanique Radio frequency identification XG
Accessory / separate part category	Connection accessories
Accessory / Separate Part Type	Connecting cable
Product or Component Type	Ethernet copper cable
Product Compatibility	XGSZ33EIP XGSZ33ETH XUW
Accessory / separate part destination	Ethernet network

Complementary

Cable length	32.81 ft (10 m)
Transmission rate	100 Mbit/s
Transmission support medium	2 twisted shielded pairs
Communication network category	5e
AWG Gauge	AWG 26
Electrical connection	1 male connector, M12 straight 4 D coding 1 male connector, RJ45 straight 4
Conductor material	Copper
Cover Material	PUR
Net Weight	0.95 lb(US) (0.43 kg)

Environment

IP Degree of Protection	IP67
Standards	ISO/IEC 11801 Ed.2, 2002 IEC 60754-1 EIA/TIA-568

Ordering and shipping details

Category	22491-SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	3389119075633
Returnability	No
Country of origin	PL

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	8.27 in (21.0 cm)
Package 1 Weight	16.16 oz (458.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	4
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	4.69 lb(US) (2.126 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Wiring Diagram

