

XGSZ24

RS232/RS485 interface, Radio frequency identification XG, RS 232/RS 485 line adaptor, for XGS K, XGS D



Main

Range of Product	Telemecanique Radio frequency identification XG
Accessory / separate part destination	XGSD XGSK XGCS
Product or Component Type	RS232/RS485 interface
Accessory / Separate Part Type	RS232C/RS485 line adaptor

Complementary

Communication port converter	RS232C/RS485 no modem signals
Connection element	RS232/RS485 interface
Current Consumption	20 mA
[Ie] rated operational current DC	20 mA
Mounting Support	35 mm symmetrical DIN rail
Product mounting	35 mm symmetrical DIN rail
Net Weight	0.23 Lb(US) (0.105 kg) 0.22 lb(US) (0.1 kg)
[Us] rated supply voltage	18...30 V DC 24 V DC
Supply voltage limits	20...30 V
Transmission Rate	<= 19200 bit/s 19200 bauds
Electrical Connection	Screw connectors

Ordering and shipping details

Category	22491-SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	3389110933611
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	2.56 in (6.5 cm)
Package 1 Length	5.12 in (13.0 cm)
Package 1 Weight	3.84 oz (109.0 g)
Unit Type of Package 2	S02
Number of Units in Package 2	28
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	7.54 lb(US) (3.422 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------