

# XUSZASL2XT

Single beam prebuilt muting arms,  
Telemecanique Safety light curtains XUSL,  
light curtain arm L 2crossed



## Main

Range of Product	Telemecanique Safety light curtains XUSL
Product or Component Type	Single-beam prebuilt muting arms
Device short name	XUSZAS
Output type	2 discrete solid-state PNP (NO)
[Sn] nominal sensing distance	0.00...8.20 ft (0...2.5 m)
Number of beams	1

## Complementary

Product Compatibility	XUSL4M
Detection system	Through beam
Product specific application	Conveyor system exit direction Conveyor system normal speed
Specific application of photoelectric detector	Detection of opaque parts
Sensing range	0...10 cm space between package > 32 cm space between package
Response Time	< 100 ms
Kit composition	Transmitter + receiver Quick start guide
Emission	IR LED
[Us] rated supply voltage	24 V DC +/- 20 %
Supply	Via connector
Current consumption	42 mA
Output voltage	24 V
Output circuit type	DC
Maximum voltage drop	<0.5 V
Local signalling	2 yellow LED receiver
Housing colour	Red RAL 3000

## Environment

Directives	98/37/EEC - machinery 89/336/EEC - electromagnetic compatibility
Product Certifications	CE
Safety reliability data	PFHd = 2.73E-7 1/h
Ambient Air Temperature for Operation	-22...131 °F (-30...55 °C)
Ambient Air Temperature for Storage	-22...158 °F (-30...70 °C)
Relative Humidity	0...95 % without condensation
IP degree of protection	IP65
Shock resistance	10 gn 16 ms IEC 61496-1
Vibration resistance	0.35 +/- 0.05 mm 10...55 Hz)IEC 61496-1

## Ordering and shipping details

Category	22455-LIGHT CURTAINS - XUSL
Discount Schedule	DS2
GTIN	3389119646406
Nbr. of units in pkg.	1
Package weight(Lbs)	3.80 lb(US) (1.722 kg)
Returnability	No


## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.71 in (14.5 cm)
Package 1 width	7.64 in (19.4 cm)
Package 1 Length	15.55 in (39.5 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	1
Package 2 Weight	4.79 lb(US) (2.172 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Dimensions



- (1): Transmitter
- (2): Receiver