



Main

Control button type	Standard momentary stop
Device Application	Conveyor systems Presses Test laboratories Woodworking equipment Transfer machines Textiles Packaging Paint lines
Device short name	XY2
Enclosure type	Dust and damp proof weatherproof enclosure indoor/ outdoor

Complementary

Line Rated Current	10 A
Cable entry	3 entries tapped for 1/2" NPT cable gland
Contact code designation	A300 Q300
Contact operation	Snap action
Contacts type and composition	2 NO/2 NC
Depth	4.1 in (104.14 mm)
Device mounting	Surface
Height	5.6 in (142.24 mm)
Installation direction	Left
Permissible voltage	300 V

Environment

NEMA degree of protection	NEMA 1/4/12
Product Certifications	CSA LR44087 class 3211 03 UL listed file E164353 CCN NKCR CE

Ordering and shipping details

Category	22441-LIMIT SWITCHES,CABLE PULL
Discount Schedule	T
GTIN	3389118132580
Returnability	No
Country of origin	MA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	3.09 lb(US) (1.4 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------