



## Main

|                                    |                                  |
|------------------------------------|----------------------------------|
| Range of Product                   | Telemecanique Cabling components |
| Accessory / separate part category | Cabling accessory                |
| Accessory / Separate Part Type     | Pre-wired connectors             |
| Series name                        | General purpose                  |

## Complementary

|                                |                                             |
|--------------------------------|---------------------------------------------|
| Electrical connection          | Straight female connector 7/8"16 UN, 3 pins |
| Cable connector fixing         | Screw-on                                    |
| Collar material                | Metal                                       |
| Status LED                     | Without                                     |
| Cable length                   | 16.40 ft (5 m)                              |
| Cable outer diameter           | 0.20 in (5 mm)                              |
| Cable composition              | 3 x 0.5 mm <sup>2</sup>                     |
| Wire insulation material       | PUR                                         |
| [Ue] rated operational voltage | 250 V AC                                    |
| Line Rated Current             | 6 A                                         |
| Contact resistance             | 5000 µOhm                                   |
| Minimum insulating resistance  | 1 GΩ                                        |
| Net Weight                     | 0.93 lb(US) (0.42 kg)                       |

## Environment

|                                       |                                                                       |
|---------------------------------------|-----------------------------------------------------------------------|
| IP Degree of Protection               | IP67                                                                  |
| Product Certifications                | cULus                                                                 |
| Ambient air temperature for operation | -31...194 °F (-35...90 °C) static<br>23...194 °F (-5...90 °C) flexing |
| Ambient Air Temperature for Storage   | -31...212 °F (-35...100 °C)                                           |

## Ordering and shipping details

|                   |                      |
|-------------------|----------------------|
| Category          | 22483-MACHINE CABLES |
| Discount Schedule | DS3                  |
| GTIN              | 3389110763423        |
| Returnability     | No                   |
| Country of origin | CZ                   |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 1.18 in (3.0 cm)       |
| Package 1 Width              | 7.09 in (18.0 cm)      |
| Package 1 Length             | 7.09 in (18.0 cm)      |
| Package 1 Weight             | 6.28 oz (178.0 g)      |
| Unit Type of Package 2       | S02                    |
| Number of Units in Package 2 | 20                     |
| Package 2 Height             | 5.91 in (15.0 cm)      |
| Package 2 Width              | 11.81 in (30.0 cm)     |
| Package 2 Length             | 15.75 in (40.0 cm)     |
| Package 2 Weight             | 8.61 lb(US) (3.904 kg) |


## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                  |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                            |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                   |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                              |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                              |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                    |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions




L : Lenght of cable

---

## Connections and Schemes

---

### Connector



BU : Blue  
BN : Brown  
BK : Black