

Product data sheet

Characteristics

ZC2JE01

Limit switch head, Limit switches XC Standard, ZC2J, without lever spring return left and right actuation



Main

Range of Product	OsiSense XC
Series name	Special format
Product or Component Type	Limit switch head
Device short name	ZC2J
Head type	Rotary head
Product Compatibility	XC2J
Associated lever	ZC2JY13 ZC2JY12 ZC2JY11 ZC2JY91 ZC2JY51 ZC2JY81 ZC2JY31
Associated body	ZC2JC2 ZC2JC28 ZC2JC18 ZC2JD2 ZC2JC1 ZC2JD1
Movement of operating head	Rotary
Type of operator	Without operating lever spring return
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	From left and right CW and CCW
Positive opening	Without
Net Weight	0.46 lb(US) (0.21 kg)
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22449-LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	3389110323887
Returnability	Yes
Country of origin	FR

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.89 in (4.800 cm)
Package 1 Width	3.74 in (9.500 cm)
Package 1 Length	1.89 in (4.800 cm)
Package 1 Weight	7.76 oz (220.000 g)
Unit Type of Package 2	S01
Number of Units in Package 2	14
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	7.28 lb(US) (3.300 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------