

# Product data sheet

## Characteristics

# ZC2JY51

Limit switch lever, Limit switches XC Standard, ZC2JY, steel square rod 3 mm, -40...120 °C



### Main

Range of Product	OsiSense XC
Series name	Special format
Product or Component Type	Limit switch lever
Device short name	ZC2J
Product Compatibility	XC2J
Associated head	ZC2JE04 ZC2JE03 ZC2JE07 ZC2JE02 ZC2JE05 ZC2JE01 ZC2JE06
Movement of operating head	Rotary
Type of operator	Rod lever spring return metal square rod 3 mm, L = 125 mm)
Type of approach	Lateral approach

### Complementary

Switch actuation	By any moving part
Positive opening	Without

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature
Ambient air temperature for storage	-40...158 °F (-40...70 °C) standard environment -40...158 °F (-40...70 °C) low temperature 50...248 °F (10...120 °C) high temperature
Environmental characteristic	High temperature Low temperature Standard environment

### Ordering and shipping details

Category	22449-LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	3389110323504
Nbr. of units in pkg.	1
Package weight(Lbs)	1.34 oz (38.0 g)
Returnability	No
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	5.12 in (13 cm)
Unit Type of Package 2	S01
Number of Units in Package 2	100

Package 2 Weight	8.77 lb(US) (3.979 kg)
Package 2 Height	5.91 in (15 cm)
Package 2 width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------