

ZCE016

Limit switch head, Limit switches XC Standard,
spring return for actuation



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Rotary head
Product Compatibility	XCKD XCKT XCKP XCMD
Associated lever	ZCY15 ZCY17 ZCY59 ZCY55 ZCY54 ZCY81 ZCY48 ZCY91 ZCY25 ZCY22 ZCY39 ZCY12 ZCY44 ZCY53 ZCY46 ZCY45 ZCY26 ZCY16 ZCY18 ZCY19 ZCY49 ZCY23 ZCY69

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Associated body	ZCT21G11 ZCMD41L5 ZCMD37L5 ZCD35 ZCMD21L2 ZCMD25L2 ZCMD41L2 ZCMD29L2 ZCMD39L5 ZCD27 ZCT28G11 ZCMD61M12 ZCMD21C12 ZCD31 ZCP28 ZCP27 ZCD25 ZCT27N12 ZCMD21M12 ZCMD37L2 ZCT25P16 ZCP29 ZCT28N12 ZCMD21L08R12 ZCMD81L2 ZCT27G11 ZCMD37L1 ZCT25N12 ZCT26P16 ZCP26 ZCP37 ZCT21P16 ZCMD39L1 ZCMD21L1 ZCD29M12 ZCMD25L5 ZCD39 ZCMD29C12 ZCD29 ZCT26G11 ZCP31 ZCP25 ZCMD29L1 ZCMD61C12 ZCMD21L5 ZCMD81L1 ZCMD41L1 ZCT26N12 ZCP21 ZCT28P16 ZCMD29L5 ZCT27P16 ZCD28 ZCP29M12 ZCP35 ZCP21M12 ZCD26 ZCMD39L2 ZCD21M12 ZCP39 ZCMD69C12 ZCMD21L08U78 ZCMD81L5 ZCD37 ZCT21N12 ZCT25G11 ZCD21 ZCMD25L1
Movement of operating head	Rotary
Type of operator	Roller plunger spring return metal
Type of approach	Lateral approach, 2 directions

Complementary

Positive opening	With
------------------	------

Environment

Ambient Air Temperature for Operation	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389119082501
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	1.38 in (3.5 cm)
Package 1 Length	1.18 in (3.0 cm)
Package 1 Weight	1.45 oz (41.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	120
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.34 lb(US) (5.145 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes