





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product Compatibility	XCKD XCKP XCMD XCKT

Associated body	ZCP35 ZCP29 ZCT27N12 ZCMD37L2 ZCD37 ZCMD81L5 ZCMD25L1 ZCP26 ZCMD39L1 ZCD31 ZCD28 ZCP39 ZCMD61M12 ZCMD81L2 ZCT26P16 ZCD21M12 ZCP21 ZCD26 ZCMD21L08U78 ZCP25 ZCT25P16 ZCP31 ZCMD37L5 ZCT28G11 ZCT21G11 ZCMD39L5 ZCT25G11 ZCD39 ZCMD41L1 ZCT21P16 ZCP28 ZCMD41L5 ZCMD81L1 ZCMD69C12 ZCMD39L2 ZCD25 ZCP27 ZCD29M12 ZCT28N12 ZCT26N12 ZCMD25L5 ZCMD21M12 ZCMD21C12 ZCD21 ZCMD21L08R12 ZCMD41L2 ZCP29M12 ZCT21N12 ZCP37 ZCMD61C12 ZCMD25L2 ZCT28P16 ZCT26G11 ZCMD21L1 ZCMD29L1 ZCMD21L5 ZCMD37L1 ZCD29 ZCMD29C12 ZCMD29L2 ZCMD21L2 ZCT27P16 ZCD27 ZCD35 ZCMD29L5 ZCP21M12 ZCT25N12 ZCT27G11
Movement of operating head	Linear
Type of operator	End plunger spring return metal adjustable)
Type of approach	Vertical approach, 1 direction

Complementary

Positive opening	With
------------------	------

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191141
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	0.81 oz (23.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------