





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product Compatibility	XCMD XCKP XCKD XCKT

Associated body	ZCT26G11 ZCD21 ZCD35 ZCT21N12 ZCMD21L5 ZCD27 ZCMD21C12 ZCMD37L2 ZCMD25L5 ZCMD21L08R12 ZCP37 ZCD29M12 ZCD25 ZCT21P16 ZCMD81L1 ZCT26N12 ZCT25G11 ZCMD41L1 ZCMD29C12 ZCP28 ZCP27 ZCMD39L5 ZCP35 ZCT28G11 ZCMD29L5 ZCT27P16 ZCMD25L1 ZCMD21L08U78 ZCMD81L2 ZCP26 ZCP29 ZCMD21L1 ZCMD41L5 ZCMD37L1 ZCMD39L1 ZCD31 ZCT21G11 ZCMD41L2 ZCD28 ZCMD21M12 ZCMD25L2 ZCMD29L2 ZCD37 ZCT27G11 ZCD29 ZCT26P16 ZCMD21L2 ZCMD37L5 ZCT28P16 ZCMD81L5 ZCD21M12 ZCP39 ZCMD61C12 ZCD39 ZCT25P16 ZCP25 ZCMD69C12 ZCMD61M12 ZCP21 ZCMD39L2 ZCT25N12 ZCP31 ZCP21M12 ZCP29M12 ZCT28N12 ZCD26 ZCMD29L1 ZCT27N12
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal with nitrile boot)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110190816
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	0.59 in (1.5 cm)
Package 1 Weight	0.60 oz (17.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------