

ZCE2A

Limit switch head, Limit switches XC Standard,
ZCE, steel roller plunger with silicone boot





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product Compatibility	XCKD XCMD XCKT XCKP

Associated body	ZCMD81L2 ZCMD21C12 ZCMD37L2 ZCD27 ZCP27 ZCD28 ZCMD29L5 ZCMD37L1 ZCT21N12 ZCD31 ZCMD29L1 ZCP37 ZCMD41L2 ZCMD39L1 ZCT26G11 ZCT21G11 ZCMD41L1 ZCMD25L1 ZCD29M12 ZCMD25L5 ZCP28 ZCMD21L08U78 ZCT27P16 ZCD21 ZCT21P16 ZCT26N12 ZCT28G11 ZCMD21L5 ZCMD21L08R12 ZCMD21M12 ZCT28N12 ZCMD81L1 ZCT27G11 ZCMD21L1 ZCT25N12 ZCT26P16 ZCP29M12 ZCP25 ZCD37 ZCT27N12 ZCMD41L5 ZCMD81L5 ZCMD21L2 ZCMD25L2 ZCD29 ZCP39 ZCD39 ZCMD61C12 ZCP21M12 ZCP35 ZCMD69C12 ZCMD39L5 ZCT25G11 ZCP26 ZCMD37L5 ZCP29 ZCD25 ZCD26 ZCD21M12 ZCP31 ZCMD61M12 ZCMD39L2 ZCT28P16 ZCMD29L2 ZCMD29C12 ZCT25P16 ZCP21 ZCD35
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal with silicone boot)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389119023597
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	1.57 in (4 cm)
Package 1 Length	0.59 in (1.5 cm)
Package 1 Weight	0.60 oz (17 g)
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	1.18 in (3 cm)
Package 2 Width	4.72 in (12 cm)
Package 2 Length	4.72 in (12 cm)
Package 2 Weight	6.00 oz (170 g)
Unit Type of Package 3	S01
Number of Units in Package 3	200
Package 3 Height	5.91 in (15 cm)
Package 3 Width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	8.02 lb(US) (3.64 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------