





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product Compatibility	XCMD XCKT XCKD XCKP

Associated body	ZCT28G11 ZCD29M12 ZCP37 ZCD21 ZCMD81L2 ZCT26P16 ZCMD69C12 ZCMD21M12 ZCMD21L08U78 ZCMD81L5 ZCD26 ZCP25 ZCMD61C12 ZCP35 ZCP29M12 ZCD25 ZCT28N12 ZCMD37L5 ZCT21P16 ZCT28P16 ZCMD39L5 ZCT25N12 ZCMD41L2 ZCMD21L08R12 ZCT27N12 ZCP21 ZCP29 ZCMD25L5 ZCP26 ZCMD21L1 ZCT25G11 ZCD39 ZCMD39L1 ZCMD21C12 ZCT21N12 ZCD27 ZCMD29L1 ZCMD21L5 ZCMD37L2 ZCD28 ZCMD41L5 ZCMD41L1 ZCT21G11 ZCMD25L2 ZCMD37L1 ZCMD81L1 ZCT26N12 ZCD29 ZCP39 ZCD31 ZCT27P16 ZCMD25L1 ZCD21M12 ZCT26G11 ZCP21M12 ZCD37 ZCP27 ZCP28 ZCMD21L2 ZCD35 ZCP31 ZCMD29L5 ZCMD61M12 ZCT27G11 ZCMD29L2 ZCT25P16 ZCMD39L2 ZCMD29C12
Movement of operating head	Linear
Type of operator	Side plunger spring return metal adjustable)
Type of approach	Vertical approach, 1 direction

Complementary

Positive opening	With
------------------	------

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191400
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.71 in (1.8 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	1.26 in (3.2 cm)
Package 1 Weight	1.94 oz (55.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------