





Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product Compatibility	XCKD XCMD XCKT XCKP

Associated body	ZCP27 ZCP39 ZCMD21C12 ZCD31 ZCT25G11 ZCMD61M12 ZCD29 ZCT26N12 ZCMD41L2 ZCT21P16 ZCP28 ZCD35 ZCMD81L1 ZCT28P16 ZCP21M12 ZCP35 ZCMD25L2 ZCT25P16 ZCMD41L5 ZCD21M12 ZCMD21L08R12 ZCD26 ZCMD21L08U78 ZCT26P16 ZCT21N12 ZCMD39L5 ZCMD41L1 ZCP29M12 ZCMD21M12 ZCMD21L2 ZCT28G11 ZCD39 ZCT21G11 ZCMD29L1 ZCMD39L1 ZCMD39L2 ZCMD29C12 ZCMD21L1 ZCD28 ZCP31 ZCP26 ZCMD81L5 ZCMD25L5 ZCMD29L2 ZCMD37L5 ZCD27 ZCT25N12 ZCMD21L5 ZCT27N12 ZCP29 ZCP37 ZCD37 ZCP25 ZCMD29L5 ZCMD69C12 ZCMD61C12 ZCT27P16 ZCD25 ZCMD25L1 ZCMD81L2 ZCT28N12 ZCT27G11 ZCD21 ZCD29M12 ZCP21 ZCMD37L1 ZCT26G11 ZCMD37L2
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal with vertical roller)
Type of approach	Vertical approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	Without

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413-LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	3389110191424
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.67 in (1.7 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	1.26 in (3.2 cm)
Package 1 Weight	2.01 oz (57.0 g)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------